

Part number for Low Power RF IC

- 品番をクリックすると、詳細ページをご覧いただけます。

IC メーカー	IC品名 or シリーズ名	ムラタ水晶振動子		
		品番	周波数	サイズ [mm]
Telink	TLSR8262 / 6 / 7 / 9, TLSR86xx	XRCGB16M000FXN20R0	16MHz	2.0 x 1.6 x 0.7
	TLSR8366	XRCGB16M000FXN22R0	16MHz	2.0 x 1.6 x 0.7
Nordic	nRF51xx	XRCGB16M000FXN16R0	16MHz	2.0 x 1.6 x 0.7
	nRF51xxx, nRF52xxx	XRCGB32M000F2P10R0	32MHz	2.0 x 1.6 x 0.7
	nRF5340	XRCGB32M000F1S2AR0	32MHz	2.0 x 1.6 x 0.7
Dialog	DA14682/3, DA1469x	XRCGB32M000F2P29R0	32MHz	2.0 x 1.6 x 0.7
	DA14531	XRCGB32M000F2P55R0	32MHz	2.0 x 1.6 x 0.7
TI	CC13xx, CC26xx	XRCGB24M000FBP12R0	24MHz	2.0 x 1.6 x 0.7
NXP	QN9080A	XRCGB32M000F2N13R0	32MHz	2.0 x 1.6 x 0.7
Renesas	RL78/G1D	XRCGB32M000F2P26R0	32MHz	2.0 x 1.6 x 0.7
Goodix	GR5515	XRCGB32M000F5N10R0	32MHz	2.0 x 1.6 x 0.7
Qualcomm	QCC51xx, QCC30xx, QCC31xx, QCC32xx	XRCGB32M000F1S2JR0	32MHz	2.0 x 1.6 x 0.7
Airoha (MediaTek)	AB155x, AB156x	XRCGB26M000F1S2ER0	26MHz	2.0 x 1.6 x 0.7
BES	BES2500Z, BES2500iZ, BES2500iUC	XRCGB26M000F1S2AR0	26MHz	2.0 x 1.6 x 0.7
	BES2500YP, BES2600	XRCGB24M000FFS1LR0	24MHz	2.0 x 1.6 x 0.7
Realtek	RTL8773B, RTL8773C, RTL8753B, RTL8753C	XRCGB40M000F1S2SR0	40MHz	2.0 x 1.6 x 0.7
Actions	ATS3015, ATS3015P	XRCGB24M000FFS1BR0	24MHz	2.0 x 1.6 x 0.7
Silicon Laboratories	EFR32xx	XRCGB38M400F1S2AR0	38.4MHz	2.0 x 1.6 x 0.7
Qprvo (Decawave)	DW1000, DW3001, DW3004	XRCGB38M400F1S2GR0	38.4MHz	2.0 x 1.6 x 0.7

- お問い合わせは下記よりお願いいたします。Contact Form : <https://www.murata.com/ja-jp/contactform>