Cylindrical Type Lithium Ion Secondary Battery US18650VTC5






Nominal Capacity*	2600 mAh
Rated (minimum) Capacity*	2500 mAh
Nominal Voltage	3.6 V
Weight (typical)	44.3 g


^{*} Charge: CCCV, 2.5 A, 4.2 V, 2.5 h, at 23deg.C Discharge: 0.2 ItA (500 mA), 2.0 V cutoff at 23deg.C

Dimensions


With tube Shape: Cylindrical









Discharge characteristics by temperature



Charge characteristics



Cycle life



Attention

^{1.} This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

^{2.} This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

As product specimental between the share a high energy density, Murata only sells lithium-ion secondary batteries to corporate customers to be embedded and sold in end products (finished products) in a form which provides the appropriate safety measures (protection circuits, etc. to prevent overcurrents and overcharding) according to the usage environment.